


Protection Mat

Indoor Use · Mat 2.0 Systems

INDOOR



Durably protect your counting mats — indoors, for all configurations.

KEY FEATURES

- P Optimal Protection**
Covers the entire installation with a 150 mm overhang on all 4 sides.
- M Durable Materials**
Regenerated ECONYL® or 100% recycled post-consumer PET — phthalate-free.
- D Two Finishes**
Standard Dark Grey or HD print: up to 100 colours and custom logos.
- S Ready in Seconds**
Tool-free, fixation-free deployment. Mat-to-Gateway connector always accessible.

TECHNICAL SPECIFICATIONS

Dimensions	1,000 × 1,300 mm to 5,500 × 1,300 mm
Overhang	150 mm minimum (4 sides)
Finishes	Dark Grey · HD Print (100 colours)
Material – Classic	ECONYL® 100% recycled nylon
Material – Custom	100% recycled post-consumer PET
Standards	ISO 14001 · phthalate-free
Configurations	10 references (1 to 10 mats)
Maintenance	Vacuum · water cleaning

INSTALLATION & USE

- 1 Prepare the installation**
Check that Mat 2.0 mats are connected and correctly positioned on the floor.
- 2 Roll out the protection mat**
Deploy flat over the entire installation. Align carefully.
- 3 Check the overhang**
Ensure a minimum 150 mm overhang on all four sides.
- 4 Verify accessibility**
The Mat-to-Gateway connector must remain accessible — do not cover it.